

Product information

11 07 160

Insulation Stripper

With opening spring, universal

IEC 60900 DIN EN 60900

- For single, multiple and fine stranded conductors with plastic or rubber insulation up to Ø 5.0 mm or 10 mm²
- Easy adjustment to the required diameter of solid or stranded wire with knurled screw and lock nut
- Special tool steel, forged, oil-hardened



⚡ 1000 V 

General	
Article No.	11 07 160
EAN	4003773015499
Pliers	chrome plated
Head	chrome plated
Handles	with dipped insulation, VDE-tested
weight	180 g
Dimensions	160 x 94 x 28 mm
Standard	DIN EN 60900 IEC 60900
Reach	yes
RohS	no

Technical details	
Style	0
Stripping capacities in square millimetres	10 mm ²
Stripping capacities (diameter)	Ø 5.0 mm
AWG	8
VDE tested	yes

Classification	
eCl@ss 5.1.4	21040302
ETIM 5.0	EC000163
ETIM 6.0	EC000163
proficl@ss 6.0	AAA002c003
UNSPSC 13.1	27111510

technical change and errors excepted