

Product information

95 21 600

Cable Shears

For two-hand operation



- For cutting copper and aluminium single conductors as well as multiple stranded cables
- Not suitable for steel wire and wire ropes
- Precision-ground, hardened blades
- Clean and smooth cut without crushing and deformation
- Favourable lever ratio due to toggle lever
- Pinch guard prevents operators' fingers being pinched
- Adjustable bolted joint
- Bolted cutter head, replaceable
- Handles: steel tube
- Cutter head: high-grade chrome vanadium electric steel, forged, oil-hardened

General

Article No.	95 21 600
EAN	4003773025252
Head	polished
Handles	with plastic grips
weight	1,862 g
Dimensions	600 x 165 x 38 mm
Reach	Nein
RohS	no

Technical details

Cutting capacity copper cable, multiple-stranded	150 mm ²
Cutting capacity copper cable, multiple-stranded	Ø 27 mm
AWG	6 / 0

Classification

eCl@ss 5.1.4	21040601
ETIM 5.0	EC000142
ETIM 6.0	EC000142
proficl@ss 6.0	EAD256c001
UNSPSC 13.1	23241616

technical change and errors excepted