

Product information

95 27 600

Cable Shears

For two-hand operation

IEC 60900 DIN EN 60900



⚡ 1000 V

- For cutting copper and aluminium single conductors as well as multiple stranded cables
- Not suitable for steel wire and wire ropes
- Precision-ground, hardened blades
- Clean and smooth cut without crushing and deformation
- Favourable lever ratio due to toggle lever
- Pinch guard prevents operators' fingers being pinched
- Adjustable bolted joint
- Bolted cutter head, replaceable
- Handles: steel tube
- Cutter head: high-grade chrome vanadium electric steel, forged, oil-hardened

General	
Article No.	95 27 600
EAN	4003773021797
Head	polished
Handles	with dipped insulation, VDE-tested
weight	2,262 g
Dimensions	600 x 180 x 45 mm
Standard	DIN EN 60900 IEC 60900
Reach	Nein
RohS	no
Technical details	
Cutting capacity copper cable, multiple-stranded	150 mm ²
Cutting capacity copper cable, multiple-stranded	Ø 27 mm
AWG	6 / 0
VDE tested	yes
Classification	
eCl@ss 5.1.4	21040601
ETIM 5.0	EC000142
ETIM 6.0	EC000142
proficl@ss 6.0	EAD256c001
UNSPSC 13.1	23241616

technical change and errors excepted