

## Product information

# 95 36 250

## Cable Cutter (ratchet action)

IEC 60900 DIN EN 60900



⚡ 1000 V 

- For cutting copper and aluminium single conductors as well as multiple stranded cables
- Not suitable for steel wire, wire ropes and fine-stranded (highly flexible) conductors
- Precision-ground, hardened blades
- Clean and smooth cut without crushing and deformation
- One-hand operation using ratchet principle
- Little handforce required due to very high transmission ratio
- Two-stage ratchet drive for easy cutting
- Simple handling as a result of low weight and compact design - can be used even in confined areas
- Pinch guard prevents operators' fingers being pinched
- High-grade special tool steel, forged, oil-hardened

### General

Article No.	95 36 250
EAN	4003773026884
Pliers	black lacquered
Handles	insulated with multi-component grips, VDE-tested
weight	652 g
Dimensions	250 x 115 x 20 mm
Standard	DIN EN 60900 IEC 60900
Reach	yes
RohS	no

### Technical details

Cutting capacity copper cable, multiple-stranded	240 mm <sup>2</sup>
Cutting capacity copper cable, multiple-stranded	Ø 32 mm
MCM	500
VDE tested	yes

### Classification

eCl@ss 5.1.4	21040301
proficl@ss 6.0	AAC484c002
UNSPSC 13.1	23241616

*technical change and errors excepted*



Ratchet principle and two-stage ratchet drive for easier cutting