

Product information

67 01 140

High Leverage End Cutting Nipper

DIN ISO 5748

- With cutting edges for soft, hard and piano wire
- High cutting capacity with little effort due to optimum coordination of cutting edge angle and transmission ratio
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



General	
Article No.	67 01 140
EAN	4003773043690
Pliers	black atramentized
Head	polished
Handles	plastic coated
weight	152 g
Dimensions	140 x 50 x 15 mm
Standard	DIN ISO 5748
Reach	no
RohS	no
Technical details	
Cutting capacities soft wire (diameter)	Ø 4 mm
Cutting capacities medium hard wire (diameter)	Ø 3.1 mm
Cutting capacities hard wire (diameter)	Ø 2.0 mm
Cutting capacities piano wire (diameter)	Ø 1.5 mm
Classification	
eCl@ss 5.1.4	21040302
ETIM 5.0	EC002222
ETIM 6.0	EC002222
proficl@ss 6.0	AAA947c004
UNSPSC 13.1	27112117

technical change and errors excepted

