

## Product information

# 14 26 160

## Diagonal Insulation Stripper

IEC 60900 DIN EN 60900

- With long cutter
- High cutting capacity due to high leverage joint
- Precision stripping holes for single conductors of 1.5 and 2.5 mm<sup>2</sup>
- Convenient cutting of NYM cables up to 5 x 2.5 mm<sup>2</sup>
- Long tips for ultra fine cutting work also in confined areas
- Induction-hardened precision blades, cutting edge hardness approx. 60 HRC
- Vanadium electric steel, forged, multi stage oil-hardened



⚡ 1000V 

### General

Article No.	14 26 160
EAN	4003773040279
Pliers	chrome plated
Head	chrome plated
Handles	insulated with multi-component grips, VDE-tested
weight	216 g
Dimensions	160 x 60 x 30 mm
Standard	DIN EN 60900 IEC 60900
Reach	no
RohS	no

### Technical details

Cutting capacities soft wire (diameter)	Ø 2.5 mm
Cutting capacities medium hard wire (diameter)	Ø 1.5 mm
Stripping capacities in square millimetres	1.5 / 2.5 mm <sup>2</sup>
AWG	16 / 14
VDE tested	yes

### Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC000163
ETIM 6.0	EC000163
proficl@ss 6.0	AAA002c003
UNSPSC 13.1	23151901

technical change and errors excepted

