

Product information

14 22 160

Diagonal Insulation Stripper



- With long cutter
- High cutting capacity due to high leverage joint
- Precision stripping holes for single conductors of 1.5 and 2.5 mm²
- Convenient cutting of NYM cables up to 5 x 2.5 mm²
- Long tips for ultra fine cutting work also in confined areas
- Induction-hardened precision blades, cutting edge hardness approx. 60 HRC
- Vanadium electric steel, forged, multi stage oil-hardened



General	
Article No.	14 22 160
EAN	4003773034988
Pliers	black atramentized
Head	polished
Handles	with multi-component grips
weight	206 g
Dimensions	160 x 53 x 21 mm
Reach	no
RohS	no
Technical details	
Cutting capacities soft wire (diameter)	Ø 2.5 mm
Cutting capacities medium hard wire (diameter)	Ø 1.5 mm
Stripping capacities in square millimetres	1.5 / 2.5 mm ²
AWG	16 / 14
Classification	
eCl@ss 5.1.4	21040302
ETIM 5.0	EC000163
ETIM 6.0	EC000163
proficl@ss 6.0	AAA002c003
UNSPSC 13.1	23151901

technical change and errors excepted

