

Product information

98 53 03

Stripping Knives

IEC 60900 DIN EN 60900

- Solid, fixed hook blade
- Suitable for round cables
- Blade: special tool steel, oil-hardened
- Ergonomically designed handle shape with comfortable slip guard
- Particularly confident grip thanks to slip-proof soft components
- Thumb recess and "finger hook" at the end of the handle ensure a good transmission of force when the blade is pulled
- Transparent protective cap



⚡ 1000 V

General	
Article No.	98 53 03
EAN	4003773026549
Handles	insulating multi-component handle, VDE-tested
weight	64 g
Dimensions	170 x 42 x 26 mm
Standard	DIN EN 60900 IEC 60900
Reach	no
RohS	no

Technical details	
Blade length	28 mm
Radius	7 mm
VDE tested	yes

Classification	
eCl@ss 5.1.4	21040602
ETIM 5.0	EC000155
ETIM 6.0	EC000155
proficl@ss 6.0	EAB554c020
UNSPSC 13.1	23241609

technical change and errors excepted