

Product information

34 32 130 ESD

Precision Electronics Gripping Pliers ESD

DIN ISO 9655 DIN EN 61 340-5



- The assortment for highest standard of performance and results
- Precision pliers for fine assembly work, e.g. in electronics and fine mechanics
- For gripping, holding and bending
- Electrically discharging handles - dissipative
- Bolted joint: precise, zero backlash operation of pliers
- Precisely finished joint surfaces for smooth, low friction movement along the complete opening range
- Low-friction double spring for gentle and even opening
- Smooth ground gripping surfaces, edges carefully deburred
- Non-reflective finish
- Low weight
- Ergonomically shaped, two-colour dual component ESD handles, black/grey
- Round, pointed jaws
- Ball bearing chrome steel, forged, multi stage oil-hardened




General

Article No.	34 32 130 ESD
EAN	4003773061670
Pliers	burnished
Head	polished
Handles	with multi-component grips
weight	62 g
Dimensions	135 x 60 x 19 mm
Standard	DIN ISO 9655 DIN EN 61 340-5
Reach	yes
RohS	no

Technical details

Style	3
	23.7 mm
	6.5 mm
Tips width (E)	2.0 mm
Tips thickness (F)	1.0 mm
Head width (A)	11.2 mm
ESD	yes



Classification

eCl@ss 5.1.4	21040301
proficl@ss 6.0	EAA840c015
UNSPSC 13.1	27112149

technical change and errors excepted