

Product information

38 11 200

- High bending strength of the pliers tips
- Straight, half-round jaws
- Vanadium electric steel; forged, oil-hardened


Mechanics' Pliers

DIN ISO 5745



General	
Article No.	38 11 200
EAN	4003773035169
Pliers	black atramentized
Head	polished
Handles	plastic coated
weight	179 g
Dimensions	200 x 53 x 13 mm
Standard	DIN ISO 5745
Reach	no
RohS	no

Technical details	
Style	1
	9.5
Tips width (W4)	3.0 mm
Tips thickness (T2)	2.5 mm
	73.0 mm
Head width (W3)	17.5 mm





Classification	
eCl@ss 5.1.4	21040301
proficl@ss 6.0	AAA004c004
UNSPSC 13.1	27112104

technical change and errors excepted