

Product information

44 31 J22

- Solid style, forged
- Non-slip, solid tips
- On basis of DIN 5256 C and DIN 5256 C, but bent 45°
- Pliers body and tips: chrome vanadium steel, forged, oil-hardened

Circlip Pliers

For internal circlips in bore holes
45° bent



∠45°

| General | |
|-------------------|--------------------|
| Article No. | 44 31 J22 |
| EAN | 4003773066965 |
| Pliers | black atramentized |
| Head | polished |
| Handles | plastic coated |
| weight | 140 g |
| Dimensions | 180 x 48 x 18 mm |
| Reach | no |
| RohS | no |
| Technical details | |
| Style | 3 |
| Size of bore | Ø 19 – 60 mm |
| Tips (diameter) | Ø 1.8 mm |
| Classification | |
| eCl@ss 5.1.4 | 21040301 |
| ETIM 5.0 | EC002228 |
| ETIM 6.0 | EC002228 |
| proficl@ss 6.0 | AAC470c002 |
| UNSPSC 13.1 | 27112140 |

technical change and errors excepted

