

## Product information

# 83 10 040

## Pipe Wrench 90°

DIN 5234

- Swedish pattern
- 90° angled jaws
- Jaws with offset teeth in opposite direction
- Teeth additionally induction-hardened
- I-beam handle design
- Captive adjusting nut
- Red powder-coated, jaws bright ground
- Chrome vanadium electric steel, forged, multi stage oil-hardened



General	
Article No.	83 10 040
EAN	4003773022336
Pliers	red powder-coated
weight	4,921 g
Dimensions	750 x 88 x 25 mm
Standard	DIN 5234
Reach	no
RohS	no

Technical details	
Clamping width	130 mm
Capacities for pipes (diameter)	Ø 5 1/8
Capacities for nuts	130 mm
Inner diameter, inches	4 Inch

Classification	
eCl@ss 5.1.4	21040301
ETIM 5.0	EC000842
ETIM 6.0	EC000842
proficl@ss 6.0	AAC492c005
UNSPSC 13.1	27111708

*technical change and errors excepted*

