

## Product information

# 83 30 015

## Pipe Wrench S-Type

DIN 5234

- Slim, S-type jaw
- Jaws with offset teeth in opposite direction
- Teeth additionally induction-hardened
- Three-point contact on pipes, self-locking
- I-beam handle design
- Captive adjusting nut
- Red powder-coated, jaws bright ground
- Chrome vanadium electric steel, forged, multi stage oil-hardened



### General

Article No.	83 30 015
EAN	4003773014256
Pliers	red powder-coated
weight	1,540 g
Dimensions	420 x 78 x 23 mm
Standard	DIN 5234
Reach	yes
RohS	no

### Technical details

Clamping width	60 mm
Capacities for pipes (diameter)	Ø 2 3/8
Capacities for nuts	60 mm
Inner diameter, inches	1 Inch

### Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000842
ETIM 6.0	EC000842
proficl@ss 6.0	AAC492c005
UNSPSC 13.1	27111708

*technical change and errors excepted*

