

Product information

83 30 020

Pipe Wrench S-Type

DIN 5234

- Slim, S-type jaw
- Jaws with offset teeth in opposite direction
- Teeth additionally induction-hardened
- Three-point contact on pipes, self-locking
- I-beam handle design
- Captive adjusting nut
- Red powder-coated, jaws bright ground
- Chrome vanadium electric steel, forged, multi stage oil-hardened



General

Article No.	83 30 020
EAN	4003773014263
Pliers	red powder-coated
weight	2,669 g
Dimensions	570 x 80 x 28 mm
Standard	DIN 5234
Reach	yes
RohS	no

Technical details

Clamping width	70 mm
Capacities for pipes (diameter)	Ø 2 3/4
Capacities for nuts	70 mm
Inner diameter, inches	2 Inch

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000842
ETIM 6.0	EC000842
proficl@ss 6.0	AAC492c005
UNSPSC 13.1	27111708

technical change and errors excepted

