

Product information

83 30 030

Pipe Wrench S-Type

DIN 5234

- Slim, S-type jaw
- Jaws with offset teeth in opposite direction
- Teeth additionally induction-hardened
- Three-point contact on pipes, self-locking
- I-beam handle design
- Captive adjusting nut
- Red powder-coated, jaws bright ground
- Chrome vanadium electric steel, forged, multi stage oil-hardened



General

Article No.	83 30 030
EAN	4003773014164
Pliers	red powder-coated
weight	4,366 g
Dimensions	680 x 87 x 31 mm
Standard	DIN 5234
Reach	yes
RohS	no

Technical details

Clamping width	100 mm
Capacities for pipes (diameter)	Ø 4 3/4
Capacities for nuts	120 mm
Inner diameter, inches	3 Inch

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000842
ETIM 6.0	EC000842
proficl@ss 6.0	AAC492c005
UNSPSC 13.1	27111708

technical change and errors excepted

