

Product information

89 01 250

Water Pump Pliers

With groove joint

DIN ISO 8976

- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Non-slip joint
- Jaw profile designed to fit screws and nuts
- Joint design reduces strain of the centre bolt, hence no wear on pivot
- Pinch guard prevents operators' fingers being pinched
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC for tool length 250 mm: high wear resistance and stable gripping
- Chrome vanadium electric steel, forged, multi stage oil-hardened



General	
Article No.	89 01 250
EAN	4003773023067
Pliers	black atramentized
Head	polished
Handles	plastic coated
weight	325 g
Dimensions	250 x 50 x 20 mm
Standard	DIN ISO 8976
Reach	no
RohS	no
Technical details	
Capacities for pipes (diameter)	Ø 1 5/16 Inch
Capacities for pipes (diameter)	Ø 34 mm
Capacities for nuts	36 mm
Classification	
eCl@ss 5.1.4	21040301
ETIM 5.0	EC000164
ETIM 6.0	EC000164
proficl@ss 6.0	AAA936c004
UNSPSC 13.1	27112112

technical change and errors excepted