

Product information

97 52 14

Crimping Pliers

Short design



- Available as accessory: locator for non-insulated open plug-type connectors
- Consistently high crimping quality thanks to precision dies and forced locking mechanism (unlockable)
- Crimping pressure has been set precisely (calibrated) in the factory, re-adjustable
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Good handling due to 20° angled head, low weight and short design
- Chrome vanadium electric steel in special quality, oil-hardened

General

Article No.	97 52 14
EAN	4003773026808
Pliers	burnished
Head	burnished
Handles	with multi-component grips
weight	387 g
Dimensions	195 x 77 x 22 mm
Reach	yes
RohS	no

Technical details

	
Applications	non-insulated open plug type connectors (plug width 2.8 + 4.8 mm)
Capacity in square millimetres	0.1 — 1.5 mm ²
Number of crimping positions	4
AWG	26 — 16

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

Accessories

97 59 14	Locator for 97 52 14
----------	----------------------

technical change and errors excepted

