

Product information

97 52 20

Crimping Pliers

Short design

- Consistently high crimping quality thanks to precision dies and forced locking mechanism (unlockable)
- Crimping pressure has been set precisely (calibrated) in the factory, re-adjustable
- Optimum transmission of force due to lever action for fatigue-reduced operation
- Good handling due to 20° angled head, low weight and short design
- Good handling due to 20° angled head, low weight and short design
- Chrome vanadium electric steel in special quality, oil-hardened



General

Article No.	97 52 20
EAN	4003773026853
Pliers	burnished
Head	burnished
Handles	with multi-component grips
weight	380 g
Dimensions	195 x 77 x 20 mm
Reach	yes
RohS	no

Technical details



Applications	Coax-, BNC- and TNC-connectors RG 58/59/62/71/223
Number of crimping positions	3
	5.4 mm / 6.48 mm / 1.72 mm
Sleeves (diameter)	Ø 6.4 / 7.6 / 2.1 mm

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

technical change and errors excepted

