

Product information

98 43 50

Torque Wrench

With driving square, reversible

ISO 3315 IEC 60900 DIN EN 60900

- Reversible for tightening of lefthanded threads
- Transparent insulated scale range 5 - 50 Nm
- Lockable torque adjustment
- Adjustable in steps of 0.25 Nm
- Easy and secure locking of attached sockets due to screw lock
- Calibration certificate included
- Chrome Vanadium steel



⚠ 1000 V 

General	
Article No.	98 43 50
EAN	4003773071778
weight	1,185 g
Dimensions	385 x 62 x 54 mm
Standard	ISO 3315 DIN EN 60900 IEC 60900
Reach	no
RohS	no

Technical details	
Square drive	1/2 mm

Classification	
eCl@ss 5.1.4	21040223
ETIM 5.0	EC002132
ETIM 6.0	EC002132
proficl@ss 6.0	AAA303c011
UNSPSC 13.1	27111715

technical change and errors excepted