

Data

Connection data

No. of poles	2
Connectable sheathed cable diameter	3.8 ... 8.2 mm
Strip length	32 mm

Geometrical Data

Width	15.6 mm / 0.614 inch
Height	13.2 mm / 0.52 inch
Depth	44.8 mm / 1.764 inch

Mechanical data

Degree of protection	IP20
----------------------	------

Material Data

Color	black
Insulating material	Polyamide 66 (PA 66)
Flammability class per UL94	V0


Fire load	0.088 MJ
Weight	2.944 g

Environmental Requirements

Surrounding air (operating) temperature	-35 ... 85 °C
---	---------------

Approvals / Certificates

Ship Approvals

Logo	Approval	Certificate name
	LR	08/20047 (E1)

UL-Approvals

Logo	Approval	Certificate name
	UL UL International Germany GmbH	E45171

Subject to changes.