

Product information

74 07 250

High Leverage Diagonal Cutter

DIN ISO 5749 IEC 60900 DIN EN 60900

- For very tough, continuous use
- High cutting performance with minimum effort due to optimum coordination of the cutting edge angle and transmission ratio
- Precision cutting edges additionally induction-hardened (cutting edge hardness approx. 64 HRC), for all sorts of wire including piano wire
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



⚡ 1000 V 



General	
Article No.	74 07 250
EAN	4003773018421
Pliers	chrome plated
Head	chrome plated
Handles	with dipped insulation, VDE-tested
weight	510 g
Dimensions	250 x 75 x 36 mm
Standard	DIN ISO 5749 DIN EN 60900 IEC 60900
Reach	no
RohS	no

Technical details	
Style	0
Cutting capacities medium hard wire (diameter)	Ø 4.6 mm
Cutting capacities hard wire (diameter)	Ø 3.5 mm
Cutting capacities piano wire (diameter)	Ø 3.0 mm
VDE tested	yes

Classification	
eCl@ss 5.1.4	21040302
ETIM 5.0	EC000165
ETIM 6.0	EC000165
proficl@ss 6.0	AAA949c004
UNSPSC 13.1	27112114

technical change and errors excepted