

Product information

74 12 160

High Leverage Diagonal Cutter

DIN ISO 5749

- For very tough, continuous use
- High cutting performance with minimum effort due to optimum coordination of the cutting edge angle and transmission ratio
- Precision cutting edges additionally induction-hardened (cutting edge hardness approx. 64 HRC), for all sorts of wire including piano wire
- With opening spring; to be activated if required
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



General	
Article No.	74 12 160
EAN	4003773065111
Pliers	black atramentized
Head	polished
Handles	with multi-component grips
weight	209 g
Dimensions	160 x 53 x 21 mm
Standard	DIN ISO 5749
Reach	no
RohS	no

Technical details	
Style	1
Cutting capacities medium hard wire (diameter)	Ø 3.4 mm
Cutting capacities hard wire (diameter)	Ø 2.5 mm
Cutting capacities piano wire (diameter)	Ø 2.0 mm

Classification	
eCl@ss 5.1.4	21040302
ETIM 5.0	EC000165
ETIM 6.0	EC000165
proficl@ss 6.0	AAA949c004
UNSPSC 13.1	27112114

technical change and errors excepted

