

Product information

25 06 160

Snipe Nose Side Cutting Pliers (Radio Pliers)

DIN ISO 5745 IEC 60900 DIN EN 60900

- Suitable for finer gripping and cutting work
- Half-round, long, tapered jaws
- Knurled gripping surfaces
- With cutting edges for soft, medium-hard and hard wire
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 61 HRC
- Vanadium electric steel, forged, multi stage oil-hardened




General

Article No.	25 06 160
EAN	4003773033806
Pliers	chrome plated
Head	chrome plated
Handles	insulated with multi-component grips, VDE-tested
weight	146 g
Dimensions	160 x 53 x 17 mm
Standard	DIN ISO 5745 DIN EN 60900 IEC 60900
Reach	no
RohS	no

Technical details

Style	0
	Ø 2.5 mm
Cutting capacities hard wire (diameter)	Ø 1.6 mm
	9.0 mm
Tips width (W4)	3.0 mm
Tips thickness (T2)	2.5 mm
	50.0 mm
Head width (W3)	16.5 mm

Technical details



Classification

eCl@ss 5.1.4	21040301
proficl@ss 6.0	EAC010c041
UNSPSC 13.1	27112134

technical change and errors excepted