



Scotch®

2000 Electrician's Duct Tape

Data Sheet



Product Description

Scotch 2000 Electrician's Duct Tape is a water resistant duct tape with polyvinyl chloride (PVC) backing and a rubber adhesive. Scotch2000 is designed to be an electrician's utility tape for holding and bundling applications.

- ❖ Easy tear
- ❖ No cloth – does not absorb water
- ❖ Clean removal (minimal residue)
- ❖ Not recommended for sealing air ducts

Test Method

Colour

Typical Value

Grey

Thickness

0.152mm (6 mils)

ASTM D-1000

Adhesion to Steel

22.3g.mm

ASTM D-1000

Tensile Strength

214g/mm

ASTM D-1000

Elongation at Break

100%

ASTM D-1000

Note: These are typical properties and should not be used for specification purposes.

Shelf Life

Scotch2000 has a three year shelf life (from date of manufacture) when stored under the following recommended storage conditions. Store behind present stock in a clean, dry place at a temperature of 21°C (70°F) and 40-50% relative humidity. Good stock rotation is recommended.

Availability

Scotch2000 duct tape is available from your local authorised 3M distributor in the following roll size:-

51mm x 46M (2 in. x 50 yds.)

Important Notice

Technical information provided by 3M is based on experience and/or tests believed to be reliable, but their accuracy is not guaranteed and the results may not be relevant to every user's application. For this reason 3M does not accept responsibility or liability, direct or consequential, arising from reliance upon any information provided and the user should determine the suitability of the products for their intended use. Nothing in this statement will be deemed to exclude or restrict 3M's liability for death or personal injury arising from its negligence. All questions of liability relating to 3M products are governed by the seller's terms of sale subject where applicable to the prevailing law. If any goods supplied or processed by or on behalf of 3M prove on inspection to be defective in material or workmanship, 3M will (at its option) replace the same or refund to the Buyer the price paid for the goods or services. Except as set out above, all warranties and conditions, whether express or implied, statutory or otherwise are excluded to the fullest extent permissible at law.

3M and Scotch are trademarks of the 3M Company. Printed in the UK.

© 3M United Kingdom PLC, 2003.

Electrical Markets Division

3M United Kingdom PLC

Sales Office

PO Box 393

Bedford MK41 0YE

Telephone: 0870 609 4639

Fax: 01234 229 433

3M Ireland Ltd

Sales Office

The Iveagh Building, The Park,

Carrickmines, Dublin 18, Ireland

Telephone: (01) 800 812 732

Fax: 353 1 280 3509

3M United Kingdom PLC

Head Office

3M Centre, Cain Road

Bracknell, Berkshire RG12 8HT

Telephone: 01344 858 000

Fax: 01344 858 758