



Scotch-WeldTM 5313 Preformed Sealant Strip

Product Data Sheet

Updated : July 2006
Supersedes : March 1996

Product Description

5313 is a tacky solid extrusion based on a synthetic rubber. The adhesive strength of 5313 is sufficient to cause cohesive failure of the sealer before loss of adhesion to the substrate, when pulled in tension.

The sealer is a non-curing type and retains the same properties and consistency after ageing in several different environments, including weathering.

Physical Properties

Not for specification purposes

Solvent	None	
Flash Point	None	
Consistency	Solid Rubber Extrusion	
Solids Content	99% by wt.	
Specific Gravity	1.3 (approx)	
Colour	Black	
Shelf Life	12 months from date of despatch by 3M when stored in the original carton at 21°C (70°F) & 50 % Relative Humidity	

Performance Characteristics

Not for specification purposes

Service Temperature Range	-29°C to 100°C (-21°F to 212°F)	
Water Resistance	Excellent	
Weathering Resistance	Excellent	
Fuel & Oil Resistance	Poor	
Compatibility Data	Supported PVC Paint (automotive enamel) (automotive lacquer)	No migration staining. } No staining, pinholing or } softening.
Compression Data	Two beads, 9mm diameter x 75mm long compressed to 0.2" at 50mm/minute. Force to compress - 35 lb 5 minute rebound height - 0.220"	

Environmental Characteristics	Ozone Resistance	No Change
	Low Temperature Flexibility (-29°C)	No Cracking
	Heat Resistance (45 minutes at 135°C)	No plasticiser migration, flow, blistering, nor loss of adhesion.

Test Method	Performance		
	Tensile Strength# (PSI, 100% cohesion failure)	Durometer# Hardness (Shore A)	Fatigue Resistance *
Ageing Cycle			
24 hours at 22°C	7	5	N/A
336 hours at 88°C	12	20	No Failure
500 hours at 38°C & 95-100% RH	9	15	N/A
500 hours at 63°C & UV Light	N/A	18	N/A
336 hours at 38°C & 95-100% RH	N/A	N/A	No Failure
336 hours at 22°C Water Immersion	N/A	N/A	No Failure

Test performed at 23°C.

* Bonds deflected 60 mils horizontally at 665 cycles per minute at -29°C after indicated ageing cycle.

("No failure" indicates 100,000 cycles tested without failure).

Directions for Use**Surface Preparation:**

In order to obtain optimum efficiency, the surfaces which are to be sealed must be dry, clean and free from grease and oil.

Application:

5313 is best applied by placing it directly on the surface to be sealed as it is removed from the roll and leaving protective liner in place until ready for final assembly, this minimises distortion and dirt pick-up.

Coverage:

Not Applicable

Drying Time:

Not Applicable

Clean Up:

Excess sealer may be removed by cutting with a sharp knife or scissors moistened with water.

Storage Conditions

Store below 22°C for maximum storage life.

Date : July 2006
5313 Preformed Sealant Strip

Additional Product Information

Test Results:

5313 has been tested by the 3M Laboratory, some of the specific tests and results are listed above. Prospective customers however, should evaluate the product to suit specific needs and end users.

Health and Safety Information

Precautions:

May cause eye irritation. Avoid eye and prolonged skin contact.

First Aid:

Eye Contact:

Immediately flush eyes with plenty of water and call a physician.

Skin Contact:

Wash affected area with soap and water.

For further Health and Safety information, please contact the Toxicology Department at Bracknell Head Office on (0344) 858000.

3M and Scotch-Weld are trademarks of the 3M Company.

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications. This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations.



Industrial Adhesives & Tapes Division

© 3M United Kingdom PLC 2000

3M United Kingdom PLC
3M House,
28 Great Jackson Street,
Manchester,
M15 4PA

Product Information :

Tel 0870 60 800 50
Fax 0870 60 700 99

3M Ireland
3M House, Adelphi Centre,
Upper Georges Street,
Dun Laoghaire, Co. Dublin,
Ireland

Customer Service :

Tel (01) 280 3555
Fax (01) 280 3509