



**Content:**

SECTION	Dia. Ø(mm)	Dia. Ø(mm)	PCS. OF COLOR				
	Before shrinking	After shrinking	BLACK	YELLOW	RED	BLUE	WHITE
1	1.2	0.6	20	20		20	
2	2.4	1.2	9	7	7	7	
3	4.8	2.5	4		4	4	4
4	9.5	5	2	2	2	2	
5	19	10	1	1	1		1
5	38	20	1				

**SPECIFICATION**

Tube Length: 50mm +/- 1mm (For full set)  
 Shrinking Ratio: 2:1  
 Operating Temperature: -50°C ~ 125°C  
 Shrinking Temperature: Start from 70°C, full recovery at 120°C  
 Flammability: VW-1

DATE		REVISION		APPROVAL BY		DRAW No		SU-1003001	
						MODEL No		SUHT119-04C	
						NAME		119pcs Color Heat -Shrink Tube Set	
						APPROVAL BY		<i>Andy</i>	
						DATE		30-09-05	
						<b>SUGO INDUSTRIAL CO., LTD.</b> TEL : 852-27901280 FAX : 852-23890688 Email : sales@sugo.com.hk			