

tesa® 60022 Spray glue EXTRA STRONG Spray glue EXTRA STRONG, 500ml

tesa® Spray Glue EXTRA STRONG 60022 is an extra strong, film-forming glue for permanently bonding materials such as fabric, plastic, cardboard, foam rubber, insulating materials, vinyl, leather, faux leather and rubber to each other or to metal and wood.

- Minimal spray mist, resistant to dampness and temperatures up to 80°C, short term 100°C
- Suitable for light as well as heavy materials with smooth to rough surfaces
- High bonding range
- Nozzle can be adjusted to desired spray quantity (H: high, M: Medium, L: Low)
- Spray direction can be set to either horizontal or vertical
- Particularly suitable for automotive applications
- Free from silicone

Main Application

tesa® Spray Glue 60022 EXTRA STRONG is typically used for versatile bonding of demanding materials like foam and fabric and is typically used by

- upholsterers
- saddlers
- automotive application

and many other professional applications in industry and craft. Furthermore, tesa® 60022 EXTRA STRONG is suitable for the general use at home.

Technical Data

▪ Color	white	▪ Solvent based on	dearomatized special petrol and acetone
▪ Temperature resistance short-term up to	100 °C	▪ Propellant based on	propane/butane
▪ Temperature resistance from	-30 °C	▪ Recommended distance of spraying	30 cm
▪ Temperature resistance up to	80 °C	▪ Recommended time before bonding	10 min
▪ Glue based on	synthetic rubber		

Properties

- | | | | |
|----------------------------|------|----------------------------|---|
| ▪ Permanent bonding result | ●●●● | ▪ Temporary bonding result | ● |
|----------------------------|------|----------------------------|---|

Evaluation across relevant tesa® assortment: ●●●● very good ●●● good ●● medium ● low

For latest information on this product please visit <http://l.tesa.com/?ip=60022>

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

tesa® 60022 Spray glue EXTRA STRONG

Spray glue EXTRA STRONG, 500ml

Additional Information

- tesa offers two complementary Spray Glues: 60021 PERMANENT and 60023 REPOSITIONABLE
- Observe the safety-information on the spray-can
- Shake can well before use and remove any dried-on glue from the nozzle
- For new applications, test suitability by gluing a sample
- The parts to be bonded must be dry and free from dust and grease. We recommend cleaning with tesa® INDUSTRY CLEANER 60040
- After use, turn can upside-down and expel glue from nozzle until only propellant comes out
- Overspray from Spray Glues can easily be removed with tesa® 60042 ADHESIVE REMOVER
- Refer to special instructions/safety data sheets: www.tesa.com/safety

For latest information on this product please visit <http://l.tesa.com/?ip=60022>

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.