

PCB TERMINAL BLOCKS

5mm Pitch Low Profile Screw Terminal

- 2-3 pole Interlocking
- 16A 250VC rating
- UL94-V0 Flame retardant PA66
- 0.3-2.5mm² (22-14AWG) solid & stranded cable
- Double tongue and groove for stronger interlocking and stability
- Captive screws
- Guided pin alignment
- Anti solder wicking
- Honed pin for smooth PCB insertion
- Test probe facility
- CE and UL approved

CTB1201



TYPE NO.	POLES	LENGTH
CTB1201/2BK	2	10mm
CTB1201/3BK	3	15mm
CTB1201/4BK	4	20mm
CTB1201/5BK	5	25mm
CTB1201/6BK	6	30mm
CTB1201/7BK	7	35mm
CTB1201/8BK	8	40mm
CTB1201/9BK	9	45mm
CTB1201/10BK	10	50mm
CTB1201/11BK	11	55mm
CTB1201/12BK	12	60mm

SPECIFICATION

Rating	16A/250V
Dielectric strength	> 2kV/60 Sec
Working temperature	-40°C to +105°C
Moulding	UL94-V0 flame retardant PA66
Pin/terminal	Brass, tin plated
Wire Protector	Phosphor bronze, nickel plated
Screw/torque	M3 steel zinc plated, 0.5Nm
Insulation Resistance	>500MΩ/DC500V
Recommended PCB hole size	ø1.2mm

