

Isotec56 Outdoor Isolating Switches



The Isotec56 series of weather protected Isolating Switches is a robust range of surface mounted switches suitable for virtually any external application.

Included in the range are single to four pole switches from 20A to 80A. The base mounted mechanism provides for easier termination and more wiring space.

Fixed Earth and Neutral connector bars with dual clamping screws provide secure clamping for all cables. Terminal bore size 5.0 - 6.6mm.

A safety feature for mounting switches to a metal structure are the insulating caps which cover the base mounting screws to totally protect them from any live cables.

Features:

- Each unit is supplied with threaded conduit plugs and reducers for easy connection to 25mm or 20mm conduits.
- Screw caps (included) must be fitted to ensure IP rating.
- Impact resistant construction will survive the hardest use in almost any installation.
- Enclosure sections are sealed with a one piece weather-seal gasket.
- A 7mm diameter hole is provided for padlocking the lever in the OFF position.
- High moulded handle barriers protect against accidental switching.
- Units comply with IEC60947-3.
- IP Rating: IP56/IP66.

- Cables in and out from top, bottom and base of switch
- Two 25mm rear knock outs in the base for surface mounting with concealed wiring
- Two 25mm screwed conduit entries top and bottom allows 4-ways to surface wire the switch.

Ordering Scheme

