

## Electronic housing - ECS-B-122X109-S-UV -V GY - 1054708

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Screw locking vented enclosure of the ECS Family. IP66/67/69 rated when mated with associated faceplate.  
Color: Grey (7042), Width: 164 mm, Height: 116 mm, Depth: 64 mm




### Your advantages

- ✓ IP66/IP67 rated with faceplate secured to the base
- ✓ Housing design supports the installation of a range of PCB thicknesses for high application diversity
- ✓ Integrated pressure compensation membrane for fluctuating ambient pressures
- ✓ Optional accessories for wall and mast mounting
- ✓ Proven PCB connection technology
- ✓ Integrated tamper protection
- ✓ Effective protection of electronics against thermal and mechanical influences
- ✓ Suitable for outdoor/indoor applications



### Key Commercial Data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 0 5 5 6 2 6 6 8 9 1 8 0
GTIN	4055626689180
Weight per Piece (excluding packing)	22.220 g
Custom tariff number	85389099
Country of origin	United States
Sales Key	ACFDAA

### Technical data

#### Item properties

Type	ECS-B-122X109-S-UV -V GY
Order No.	1054708
Housing type	outdoor housings

# Electronic housing - ECS-B-122X109-S-UV -V GY - 1054708

## Technical data

### Item properties

Type	integrated pressure compensation membrane
Max. NEMA code to attain	6
IK code	IK08
Impact strength	IK08
Mounting type	Wall or panel mount. Pole mount with accessory.
Ventilation	integrated pressure compensation membrane
Type of locking	screw locking

### Measurements

Width [ w ]	164 mm
Height [ h ]	116 mm
Depth [ d ]	64 mm

### Material specifications

Housing material	PC (polycarbonate)
Color (RAL)	gray (7042)
Flammability rating according to UL 94	V0

### Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 100 °C
Ambient temperature (operation)	-40 °C ... 100 °C

### PCB data

Number of PCB holders	1
PCB thickness	1.57 mm ... 2.36 mm

### Power dissipation, single housing at 20°C

Ambient temperature	20 °C
Reduction factor	1
Mounting position	vertical
Power dissipation	19 W

### Salt mist

Test duration	96 h
---------------	------

### General information

Note	Refer to the data sheet for the range in the download area.
------	---

### Packaging information

Pieces per package	5
Denomination packing units	Pcs.

### Standards and regulations

Flammability rating according to UL 94	V0
--	----

### Environmental Product Compliance

# Electronic housing - ECS-B-122X109-S-UV -V GY - 1054708


## Technical data

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Drawings

### Dimensional drawing



## Classifications

### eCl@ss

eCl@ss 10.0.1	27182702
eCl@ss 11.0	27182702
eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180505
eCl@ss 5.1	27180505
eCl@ss 6.0	27180800
eCl@ss 7.0	27182702
eCl@ss 9.0	27182702

### ETIM

ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 6.0	EC001031
ETIM 7.0	EC001031

### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501

## Electronic housing - ECS-B-122X109-S-UV -V GY - 1054708

### Accessories

#### Additional products

Front plate - ECS-P-122X169-S-UV-B GY - 1050382



Screw locking blank faceplate of the ECS Family. IP66/67/69 rated when mated with associated enclosure. Color: Grey (7042), Width: 163 mm, Height: 30 mm, Depth: 62 mm

Front plate - ECS-P-122X169-S-UV-1M12 GY - 1050381



Screw locking one female M12 faceplate of the ECS Family. IP66/67/69 rated when mated with associated enclosure. Color: Grey (7042), Width: 163 mm, Height: 30 mm, Depth: 62 mm

Front plate - ECS-P-122X169-S-UV-CG GY - 1050380



Screw locking cable gland faceplate of the ECS Family. IP66/67/69 rated when mated with associated enclosure. Color: Grey (7042), Width: 163 mm, Height: 30 mm, Depth: 62 mm

Front plate - ECS-P-122X169-S-UV-2M12 GY - 1050379



Screw locking two female M12 faceplate of the ECS Family. IP66/67/69 rated when mated with associated enclosure. Color: Grey (7042), Width: 163 mm, Height: 30 mm, Depth: 62 mm

Safety clip - ECS-BL - 2230012



PCB safety clip

## Electronic housing - ECS-B-122X109-S-UV -V GY - 1054708

### Accessories

Mounting brackets - ECS-PM - 2230013



Mounting set for mast mounting

---

Phoenix Contact 2021 © - all rights reserved  
<http://www.phoenixcontact.com>