



Product Data Sheet

Folding Probe

Foldable thermometer with stainless steel sensor probe, adjustable from 0 to 180 degrees, to allow different angle viewing. Suitable for a variety of uses including HVAC, food processing, agriculture, laboratory and energy management.

The probe folds away conveniently for easy storage when not in use.

Probe thermometers can be supplied with UKAS Calibration Certificate or Statement of Conformity on request.



Auto switch off when probe is closed to less than 30° angle.

Product Features

- Foldable probe for convenient use and easy storage
- Stainless steel probe adjusts from 0° to 180°
- Protection to IP 65
- One second temperature sensing time
- Auto power on when probe is opened more than 30° angle
- Auto power off when probe is closed less than 30° angle
- Wrist strap and battery included

Product Specifications

Temperature Range:	-50 to +250°C/°F (switchable)
Accuracy:	±1°C between -20°C and +150°C, otherwise ±2°C
Resolution:	0.1°C
Battery:	LR44 x 1 pc
CE:	Approved
ROHS/WEEE:	Compliant
Hazard Information (SDS):	See www.brannan.co.uk for information
LCD Dimensions:	15mm x 32mm
Probe Length:	85mm
Probe Diameter:	3.5mm ø
Product Dimensions:	45mm x 125mm x 18mm (with probe closed)
Product Weight:	Gross - 85g Net - 50g (incl. battery & wrist strap)
Display Card Weight:	5g
Display Card Dimensions:	171mm x 130mm
Display PVC Blister Weight:	30g
Display PVC Blister Dimensions:	209mm x 145mm x 25mm



Description	Barcode	Product No
Folding Probe Thermometer	5 011405 311757	31/175/0

PDS 0272:15:R2

Please note: all information on this data sheet is correct at the time of printing, but our policy is one of continuous product development. We reserve the right to change specification without notice.



S.Brannan & Sons Ltd

Leconfield Industrial Estate Cleator Moor Cumbria CA25 5QE UK
Tel: +44 (0) 1946 816600 Fax: +44 (0) 1946 816625 email: sales@brannan.co.uk web: www.brannan.co.uk

