






Rating	20A 32VDC  20A 250VAC 
Insulation R	DC 500V 100M ohm Min.
Voltage Breakdown	AC 1000V 1 minute
Fuse Size	ø5.2*20mm

No Fuse




TOLERANCE: ±0.3mm UNLESS OTHERWISE SPECIFIED.

D:\Ruby\Projects\■■■\R1~R10

							△
							△
Date	Name	Descriptions					NO
Drawing	Check	Approval	SCI No.	1310283	Model Name	FUSE HOLDER	
徐洲迎			Customer No.		Model No.	R3-32A1	
9/18/'06	9/18 '06		Unit	mm			

Rating	20A 32VDC cRU _{US} 20A 250VAC RU
Insulation R	DC 500V 100M ohm Min.
Voltage Breakdown	AC 1000V 1 minute
Fuse Size	ø6.0*30mm ø6.3*32mm

No Fuse



TOLERANCE: ±0.3mm UNLESS OTHERWISE SPECIFIED.

D:\Ruby\Projects\■■\R1~R10

							△
							△
Date	Name	Descriptions					NO
Drawing	Check	Approval	SCI No.	1310284	Model Name	FUSE HOLDER	
徐洲迎	<i>[Signature]</i>		Customer No.		Model No.	R3-32B1	
9/15/'06	9/18-'06		Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.		