


Art.- No.	Bemessungswerte/Ratings/Valeurs assignées			Spannungsfall Voltage drop Chute de tension max [mV]	Verlustleistung Sustained dissip. Valeur de dissip. max [W]	Schmelzintegral Melting integral Intégral de fusion [A ² s]	
	Strom Current Courant	Spannung Voltage Tension	Ausschaltvermögen Breaking capacity Pouvoir de coupure				
520.504	50 mA	250 V	1500 A	10.000	1,6	auf Anfrage/ on request/ à demande	
520.505	63 mA			8.800			
520.506	80 mA			7.600			
520.507	100 mA			7.000			
520.508	125 mA			5.000			
520.509	160 mA			4.300			
520.510	200 mA			3.500			
520.511	250 mA			2.800	2,5		0,20
520.512	315 mA			2.500			
520.513	400 mA			2.000			
520.514	500 mA			1.800			
520.515	630 mA			1.500			
520.516	800 mA			1.200			
520.517	1 A			1.000			
520.518	1,25 A			800	4	0,63	
520.519	1,6 A			600		1,28	
520.520	2 A			500		5,36	
520.521	2,5 A			400		7,63	
520.522	3,15 A			350		5,95	
520.523	4 A			300		9,28	
520.524	5 A			250		45,00	
520.525	6,3 A			200		78,59	
520.526	8 A			200		125,44	
520.527	10 A			200		200,00	

Aufbau: Keramikrohr, mit Löschmittel
Kontaktkappen: Messing, vernickelt
Verpackung: 100 St. = 10 x 10 Faltschachteln
1000 St. = Industrieverpackung

Construction: Ceramictube, with extinguishing agent
Contact caps: Brass, nickel plated
Packing: 100 pcs. = 10 boxes of 10 pieces
1000 pcs. = Industrial boxes

Construction: Tube céramique avec moyen d'extinction
Cabochons de contact: Laiton, nickelé
Emballage: 100 pcs. = en 10 boîtes de 10 pièces
1000 pcs. = en emballage industriel

Strom-Zeit-Kennlinien
Current Time Characteristics
Caractéristique courant/temps



Schmelzzeit-Grenzwerte / Pre-arcing time limits / Temps de fusion limité

Bemessungsstrom Rated Current Courant assigné	2,1 I _{rat} max.	2,75 I _{rat} min. max.	4 I _{rat} min. max.	10 I _{rat} max.
0,05 - 6,3 A	30 min	10 ms 2 s ¹⁾	3 ms 300 ms	20 ms
8 A + 10 A	30 min	40 ms 20 s	10 ms 1 s	30 ms

1) 3 s für Bemessungsströme 4-6,3 A / 3 s for rated currents 4-6,3 A / 3 s pour courant assignées 4-6,3 A

2) auf Anfrage / on request / à demande