

EAO – Your Expert Partner for Human Machine Interfaces

84-5340.0020 - Emergency stop switch - Emergency stop switch

84-5340.0020 - Emergency stop switch - Emergency stop switch



Attention: The preview is based on a sample product. This can differ from your current configuration.

Attribute

Design	raised
Front dimension	Ø 32 mm
Front form	round
IP front protection	IP65, IP66, IP67
Mounting cut-out	Ø 22.3 mm
Contacts	2 NC
Contact material	Gold
Front dimension	Ø 32 mm
Housing colour	Yellow
Housing material	Plastic
IP Protection	IP20 rear side
Lens colour	Red
Lens illumination	non illuminative
Lens material	Plastic
Lens optics	opaque
Lens shape	mushroom-head
Operating Travel	Ca. 4 mm
Switching action	Maintained
Switching system	Slow-make switching element
Switching voltage	250 V
Terminal	Plug-in terminal
Weight	0.028 kg


Function

Emergency stop switch


EAO – Your Expert Partner for Human Machine Interfaces

84-5340.0020 - Emergency stop switch - Emergency stop switch


Dimensions




Mounting cut-outs



Component layouts



Wiring diagrams



Additional information

Lens plastic red

Contacts: NC = Normally closed, NO = Normally open

Contacts: NC = Normally closed, NO = Normally open

Twist to unlock clockwise, position indication ring green