


BEAKER RANGE

LabValue - Beakers Glass, Low Form with Spout



- » Beakers feature chemically resistant white graduations
- » Spout for easy pouring.
- » Uniform walls provide excellent strength against breakage.
- » Borosilicate 3.3 glass has the following heat tolerances:
 Strain Point -515°C | Annealing Point 565°C | Softening Point 820°C.

Code	Capacity	Pack Size	
EGL0126D	50 ml	12	
EGL0126E	100 ml	12	
EGL0126F	150 ml	12	
EGL0126H	400 ml	6	
EGL0126I	500 ml	6	
EGL0126J	600 ml	6	
EGL0126J8	800 ml	6	
EGL0126K	1000 ml	6	



Tel.: 585.563.7963

Fax.: 585.486.1735

E-mail: sales@eiscoindustrial.com