

Product Description

Enables the use of cable glands with larger connection threads than the existing threaded holes; Assembling with a wrench; Supporting surface for spanner means scratches on the housing are avoided



Application range

- Machines
- Devices
- Housings

Benefits

- Enables the use of cable glands with larger connection threads than the existing threaded holes
- Assembling with a wrench
- Supporting surface for spanner means scratches on the housing are avoided

Design

- Metric connection thread acc. to EN 50262



Technical Data

Colour delivered

Light grey (RAL 7035)

Temperature range

-40°C to +100°C

Material

Polyamide, glass fibre-reinforced

Article List

Part number	Thread/ male M1	Thread/ female M2	SW (mm)	Pieces / PU
SKINDICHT® EKU-M				
52100300	12 x 1.5	16 x 1.5	20	100
52100301	16 x 1.5	20 x 1.5	24	100
52100302	20 x 1.5	25 x 1.5	29	100
52100303	25 x 1.5	32 x 1.5	36	50
52100304	32 x 1.5	40 x 1.5	46	25
52100305	40 x 1.5	50 x 1.5	55	10
52100306	50 x 1.5	63 x 1.5	68	10

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.