HAND HELD CASES

87 Series Silicone Cover Enclosure

Hand-held Enclosure, suitable for measuring instruments, testing devices, wireless communication devices, medical devices etc.

- Silicone cover accessory available.
- Available in six sizes, plain and battery compartments versions. (further battery compartment options available upon request)
- Available in two colours: off-white & dark grey.

SPECIFICATION	
Materials	Lid & base high impact ABS-UL94-V0
Operating temperature	-10°C to +60°C
Standard colours	Off-White & Dark grey
Standard unit includes:	Lid and Base, self-tapping screw
Options	Silicon case in red, yellow, blue and dark grey

UNIVERSAL ENCLOSURES

HAND HELD CASES

HEAVY DUTY ENCLOSURES

> DIN RAIL BOXES

INTERFACE

CONTROL STATIONS

DIECAST & METAL BOXES

DESKTOP & INSTRUMENT CASES

POTTING BOXES

19" ENCLOSURES

CABINETS

DEVELOPMENT BOARDS

> CUSTOM SIZED ENCLOSURES

> > CUSTOM SERVICES





Without Battery Compartment


DARK GREY	OFF-WHITE	LENGTH	WIDTH	HEIGHT
CHH871DGN	CHH871WHN	115mm	69mm	19.5mm
CHH872DGN	CHH872WHN	115mm	69mm	28mm
CHH873DGN	CHH873WHN	135mm	76mm	27mm
CHH874DGN	CHH874WHN	135mm	76mm	35mm
CHH875DGN	CHH875WHN	165mm	80mm	27mm
CHH876DGN	CHH876WHN	165mm	80mm	35mm

With Battery Compartment

DARK GREY	OFF-WHITE	LENGTH	WIDTH	HEIGHT	BATTERY COMPARTMENT
CHH871DGA	CHH871WHA	115mm	69mm	19.5mm	2 x AAA
CHH872DGB	CHH872WHB	115mm	69mm	28mm	2 x AA
CHH873DGB	CHH873WHB	135mm	76mm	27mm	2 x AA
CHH874DGB	CHH874WHB	135mm	76mm	35mm	2 x AA
CHH875DGC	CHH875WHC	165mm	80mm	27mm	4 x AA
CHH876DGC	CHH876WHC	165mm	80mm	35mm	4 x AA

Silicone Cover

- Flexible open faced removable silicon rubber cover
- Fits tightly over base, sides and around edges of lid
- Custom colours available from MOQ 500 pcs per order, just provide us with your pantone colour.



RED	YELLOW	BLUE	DARK GREY	LENGTH	WIDTH	HEIGHT
CHH87C1RD	CHH87C1YL	CHH87C1BL	CHH87C1DG	120mm	74mm	24mm
CHH87C2RD	CHH87C2YL	CHH87C2BL	CHH87C2DG	120mm	74mm	32.5mm
CHH87C3RD	CHH87C3YL	CHH87C3BL	CHH87C3DG	141mm	81mm	32mm
CHH87C4RD	CHH87C4YL	CHH87C4BL	CHH87C4DG	141mm	81mm	40mm
CHH87C5RD	CHH87C5YL	CHH87C5BL	CHH87C5DG	171mm	85mm	32mm
CHH87C6RD	CHH87C6YL	CHH87C6BL	CHH87C6DG	171mm	85mm	40mm

