

EAN/GTIN:	4013288113924	Dimension:	255x210x62 mm
Part no.:	05074739001	Weight:	1145 g
Article no.:	7440/41/42	Country of origin:	CZ
		Customs tariff number:	82079030

- Kraftform torque screwdriver set
- Suitable for bits with 1/4" hex head drive
- With Hex-Plus, TORX® and TORX PLUS® bits
- In a stable case

Wera torque screwdriver set. Two high precision torque screwdrivers with variable torque settings. One torque screwdriver with Kraftform pistol handle for the transfer of especially high torque; multi-component for high working speeds and particularly ergonomic screwdriving. Simple adjustment of the required torque value without any special tools. Easy-to-read scale value. Rapidaptor quick-release technology for rapid bit change. Unlimited torque to loosen seized screws. Multi-component Kraftform handle with hard and soft zones for high working speeds, whilst being easy on the hand. Includes a bit assortment in a high quality and stable plastic case.

Weblink



http://products.wera.de/en/torque_tools_series_7400_kraftform_torque_screwdrivers_variable_torque_adjustment_models_7440_41_42.html



Wera - 7440/41/42
05074739001 - 4013288113924



Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de



Series 7400 Krafftform Torque Screwdrivers



Content:

	7400	
	05074700001	1 x 7440x1/4x0.3-1.2
	05074701001	1 x 7441x1/4x1.2-3.0

	7400 Pistole	
	05074702001	1 x 7442x3.0-6.0

	867/1 TZ TORX®	
	05066301001	1 x TX 6x25
	05066302001	1 x TX 7x25
	05066303001	1 x TX 8x25
	05066304001	1 x TX 9x25
	05066305001	1 x TX 10x25
	05066308001	1 x TX 15x25
	05066310001	1 x TX 20x25
	05066312001	1 x TX 25x25
	05066315001	1 x TX 30x25

	867/1 IP TORX PLUS®	
	05066274001	1 x 6 IPx25
	05066276001	1 x 7 IPx25
	05066278001	1 x 8 IPx25
	05066279001	1 x 9 IPx25
	05066280001	1 x 10 IPx25
	05066282001	1 x 15 IPx25
	05066284001	1 x 20 IPx25
	05066286001	1 x 25 IPx25
	05066288001	1 x 30 IPx25

	840/1 Z Hex-Plus	
	05056305001	1 x 2.0x25
	05056310001	1 x 2.5x25
	05056315001	1 x 3.0x25
	05056320001	1 x 4.0x25
	05056325001	1 x 5.0x25
	05056330001	1 x 6.0x25

Adjustable Torque Screwdrivers

Simple setting

Easy-to-read



Wera's adjustable torque screwdrivers allow variable torque settings with maximum precision and ensure that the user gets the very best results in the familiar Wera design with superior ergonomics.



Simple setting of the required torque by hand.



Easy-to-read scale value.

Weblink

http://products.wera.de/en/torque_tools_series_7400_krafftform_torque_screwdrivers_variable_torque_adjustment_models_7440_41_42.html

Wera - 7440/41/42
05074739001 - 4013288113924

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Series 7400 Kraffform Torque Screwdrivers

Measurement accuracy



Measurement accuracy is $\pm 6\%$ in accordance with the standard DIN EN ISO 6789. Distinctly audible and noticeable excess-load signal when the pre-set torque is reached.

Versatile



Rapidaptor technology makes the tool adaptable since bits and sockets can be exchanged rapidly.

Rapid-in and self-lock



The bit can be pushed into the adaptor without moving the sleeve. The lock is activated automatically as soon as the bit is applied to the screw. Bits are held securely and wobble-free.

Rapid-out



Simply push the sleeve forward to change the bit. The spring mechanism lifts the bit off the magnet and unlocks the tool. The bit can be easily removed. The rapid-out function makes it easy to remove even the smallest bits without extra tools.

Weblink

http://products.wera.de/en/torque_tools_series_7400_kraffform_torque_screwdrivers_variable_torque_adjustment_models_7440_41_42.html

Wera - 7440/41/42
05074739001 - 4013288113924

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de