

## 300 IP TORX PLUS® torque-indicator, 7 IP, 0.9 Nm

Series Torque-indicators



<b>EAN/GTIN:</b>	4013288093394	<b>Dimension:</b>	170x37x37 mm
<b>Part no.:</b>	05028041001	<b>Weight:</b>	116 g
<b>Article no.:</b>	300 IP	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82054000

- Torque -indicator with pre-set and tamperproof torque value
- Distinct audible and perceivable excess load signal when the pre-set torque value is reached
- Non-adjustable and tamperproof
- Unlimited torque for loosening seized screws
- Multi-component Kraftform handle for fast and ergonomic screwdriving

Wera torque screwdriver with fixed torque for recessed TORX PLUS® screws. Tamperproof and with a slim hex blade. Unlimited torque for loosening seized screws. Multi-component Kraftform handle for pleasant, ergonomic working that prevents blisters and calluses. Hard gripping zones for high working speeds whereas soft zones ensure high torque transfer.

### Weblink

[http://products.wera.de/en/torque\\_tools\\_series\\_torque-indicators\\_300\\_ip.html](http://products.wera.de/en/torque_tools_series_torque-indicators_300_ip.html)

Wera - 300 IP  
05028041001 - 4013288093394

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

Torque-indicators




Wera torque-indicators have been factory pre-set to values recommended by leading carbide tool manufacturers. These tightening values relate specifically to the size of the TORX®, TORX PLUS® or hexagon socket screw. Torque indicators ensure safe and easy loosening of screw connections. Precision :  $\pm 10\%$

Torque-indicators




Suitable for applications requiring a non-adjustable i.e. a tamperproof torque blade assembly.

Torque-indicators




Some screw connections require specific torque values so that they can be tightened or loosened easily. Wera torque-indicators are pre-set to torque values recommended by leading carbide tool manufacturers. Pre-set torque between 0.6 Nm and 5.0 Nm, for TORX®, TORX PLUS® and hexagon socket screws, unlimited loosening torque, two handles, tamper-proof.

Precisely adjusted



Torque blade assembly precisely adjusted to the respective screw size for the TORX®, TORX PLUS® and hexagon socket screw profiles.

For difficult-to-access places



Slim 4 mm hexagon blades to reach screws in difficult-to-access places.

Tamperproof



Non-adjustable and tamperproof.

Excess-load signal



Distinctly audible and noticeable excess-load signal when the pre-set torque is reached.

Weblink

[http://products.wera.de/en/torque\\_tools\\_series\\_torque-indicators\\_300\\_ip.html](http://products.wera.de/en/torque_tools_series_torque-indicators_300_ip.html)

Wera - 300 IP  
05028041001 - 4013288093394

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: info@wera.de

More variants of this product family:



		nm	ft. lb.	mm	mm	mm	mm	inch
05028040001	6 IP	0.6	0.4	4	3.5	65	105	2 9/16
<b>05028041001</b>	<b>7 IP</b>	<b>0.9</b>	<b>0.7</b>	<b>4</b>	<b>3.5</b>	<b>65</b>	<b>105</b>	<b>2 9/16</b>
05028042001	8 IP	1.2	0.9	4	3.5	65	105	2 9/16
05028043001	9 IP	1.4	1.0	4	3.5	65	105	2 9/16
05028044001	10 IP	2.0	1.5	4	3.8	65	105	2 9/16
05028045001	15 IP	3.0	2.2	4	3.8	65	105	2 9/16

**Weblink**

[http://products.wera.de/en/torque\\_tools\\_series\\_torque-indicators\\_300\\_ip.html](http://products.wera.de/en/torque_tools_series_torque-indicators_300_ip.html)

Wera - 300 IP

05028041001 - 4013288093394

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)