



WEEKLY TIME SWITCH PROFI DIGITAL 230V 16A
1CHANNEL 2MW

Similar to image

Technical data:		
Design of the switching function		CO contact
Type of mounting		DIN rail
Type of voltage / of supply voltage		AC
Protection class IP		IP20
Depth	mm	70
Height	mm	83
Width	mm	36
Accuracy / per day	s	0.1
Plus petit intervalle de temps de commutation / de la voie 1	s	1
Product feature		
• external switch input		No
• potential-free switching contact		Yes
Product function		
• 24-hour time program		Yes
• Automatic daylight-saving adjustment		Yes
• Holiday time program		Yes
• Switching preselection		Yes
• Weekly time program		Yes

• 60 min time program • Operating hours counter • annual time program • Random time program • Cyclical time program • Astro program • Impulse program • Text guidance in display • direct operation		Yes
		Yes
		No
		Yes
		Yes
		No
		Yes
		Yes
		Yes
Mode de fonctionnement		
• radiocommandé • synchronisation réseau • commande piézo-électrique		No
		Yes
		No
Supply voltage		
• initial value • final value	V	230
	V	230
Supply voltage frequency	Hz	50 ... 60
Number of pitch units for width		2
Number of channels		1
Number of memory slots		56
Switching capacity current / at 250 V / with AC / nominal value	A	16
Item designation		
• according to DIN EN 61346-2 • according to DIN EN 81346-2		K
		K

Certificates/approvals:

General Product Approval	other
---------------------------------	--------------



[other](#)

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/lowvoltage/mall>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/7LF4521-0/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=7LF4521-0

last change:

Aug 12, 2013