

Beam pattern:



Features:

- 45° focusing angle

Applications:

- Non long range lighting with medium area

Specification:

Item	Value
Transmittance	93%
Material	PMMA
Standard	SGS/ROHS
Temperature	-35°C-90°C
Surface treatment	Matt

Outline dimension:

