

### Product specification for LED lens:

Specification	Φ100*12.7
Perspective	30
Wick	9
Material	PMMA
Transmittance	93%
Temperature	-35°C-90°C
Weight	50g
Tolerance	±0.2mm
Standard	SGS/ROHS
Surface treatment	P



### Outline dimensions:

