



SIMATIC S7-1200,
COMMUNICATION MODULE CM 1241, RS232,
9 PIN SUB D (MALE),
SUPPORTS MESSAGE BASED FREEPORT

Supply voltage	
24 V DC	Yes
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Input current	
Current consumption, max.	220 mA ; From L5+; logic
Power losses	
Power loss, typ.	1.1 W
Interfaces	
Number of interfaces	1
Interface physics, RS 232C (V.24)	Yes
Point-to-point	
Cable length, max.	10 m
Climatic and mechanical conditions for storage and transport	
Climatic conditions for storage and transport	
Free fall	
Drop height, max. (in packaging)	0.3 m ; five times, in dispatch package
Temperature	

Permissible temperature range	-40 °C to +70 °C
Air pressure acc. to IEC 60068-2-13	
Permissible air pressure	1080 to 660 hPa
Relative humidity	
Permissible range (without condensation) at 25 °C	95 %
Mechanical and climatic conditions during operation	
Climatic conditions in operation	
Temperature	
Permissible temperature range	-20 °C to +60 °C horizontal mounting, -20 °C to 50 °C vertical mounting, 95% humidity, non-condensing
Permissible temperature change	5°C to 55°C, 3°C / minute
Air pressure acc. to IEC 60068-2-13	
Permissible air pressure	1080 to 795 hPa
Software	
Runtime software	
Target system	
S7-1200	Yes
Dimensions	
Width	30 mm
Height	100 mm
Depth	75 mm
Weights	
Weight, approx.	150 g
Status	Jun 19, 2014