

## Classic Globe (GLS) Omni-Lamp 6.2W (60W) 2700K 806lm E27 Non-Dimmable 320 deg Beam Angle

Quick Order Code: 737616 / Page: 1



### Product Details

Partcode: ILA60E27C6.2N27KCIWA

Quick Order Code: 737616

Range Name: Mensae

Placement / Application: Indoor, General Lighting

Market Segment: Commercial indoor, Residential indoor

Product Type: GLS

Warranty: 2 Years

CE / RoHS: Yes

### Physical Data

Lamp Base: E27

Base Type: Edison screw

Base Colour: Matt white

Globe Type: Classic Globe (GLS)

Globe Finish: Clear

Material: Glass

**Physical Data**

Length: 108mm  
Width: 60mm  
Weight (Unpackaged Single Unit): 32g  
Lamp or Luminaire Shape: Round  
Lamp Fixing: Pendant, Wall

**Electrical Data**

Voltage Range: 220-240V  
Power Consumption: 6.2 Watts  
Driver included: Yes  
Driver IC Manufacturer: Mingwei  
Electric Current: AC  
Ampage: 50.00mA  
Frequency Range: 50 Hz  
Power Factor:  $\geq 0.50$   
Wattage Equivalent: 60 Watts  
Dimming: Non-dimmable  
LVD Certified: Yes  
EN: EN-62560

**Light Data**

Lumens: 806lm  
Lumens per Watt: 130.0lm/W  
Beam Angle: 320°  
Correlated Colour Temperature (CCT): 2,700k  
Colour Temperature: Warm  
Colour Rendering Index (CRI):  $\geq 80$   
LED Manufacturer: Hangke  
LED Type: Filament chip  
Instant on - Less than 1 second: Yes  
Lifetime: 15,000 hrs  
Switching Cycles:  $>7,500$  X

### Environmental

Energy Rating: A++

Lowest Operating Temperature: -20 degrees

Maximum Operating Temperature: 40 degrees

IP (Ingress Protection) Rating: IP20

Hg 0% (Mercury Free): Yes

### Packaging



EAN Barcode (unit of 1): 5055788212379

Packaged Weight (Unit of 1): 80g

Length (unit of 1): 135mm

Width (unit of 1): 68mm

Depth (unit of 1): 68mm

**Outer packaging info available on website**

*Product data last updated on: Friday, May 13, 2016 - 13:28*