

Mini Globe Omni-Lamp 2W (25W) 2700K 250lm B22 Non-Dimmable 300 deg Beam Angle*Quick Order Code: 375968 / Page: 1*

This cutting edge A++, 2W retro-fit Integral LED Mini Globe (large bayonet base) from the Omni-Lamp range delivers a warm white light and brightness, similar to a 25W filament bulb. It has the appearance, feel and weight of a traditional light bulb. Featuring an LED filament, which enables a super-wide 300 degree beam angle. A decorative lamp ideal for living rooms, dining rooms, bedrooms and hotels, in classic or modern wall or floor/table lamp fittings.

Product Details

Partcode: ILP45B22C2.0N27KCCWA

Quick Order Code: 375968

Range Name: Omni

Product Type: Mini Globe

Warranty: 2 Years

CE / RoHS: Yes

Physical Data

Lamp Base: B22

Base Type: Bayonet cap

Globe Type: Mini Globe

Globe Finish: Clear

Material: Glass

Physical Data

Length: 70mm

Width: 45mm

Weight (Unpackaged Single Unit): 19g

Lamp or Luminaire Shape: Round

Lamp Fixing: Pendant, Wall

Electrical Data

Voltage Range: 220-240V

Power Consumption: 2.0 Watts

Driver included: Yes

Electric Current: AC

Ampage: 19.00mA

Frequency Range: 50 Hz

Power Factor: ≥ 0.45

Wattage Equivalent: 25 Watts

Dimming: Non-dimmable

LVD Certified: Yes

EN: EN-62560

Light Data

Lumens: 250lm

Lumens per Watt: 125.0lm/W

Beam Angle: 300°

Correlated Colour Temperature (CCT): 2,700k

Colour Temperature: Warm

Colour Rendering Index (CRI): ≥ 80

LED Type: Filament chip

Instant on - Less than 1 second: Yes

Lifetime: 15,000 hrs

Switching Cycles: $>7,500$ X

Environmental

Energy Rating: A++

Lowest Operating Temperature: -20 degrees

Maximum Operating Temperature: 40 degrees

IP (Ingress Protection) Rating: IP20

Hg 0% (Mercury Free): Yes

Packaging



EAN Barcode (unit of 1): 5055788210986

Packaged Weight (Unit of 1): 34g

Length (unit of 1): 85mm

Width (unit of 1): 50mm

Depth (unit of 1): 50mm

Outer packaging info available on website

Product data last updated on: Friday, May 13, 2016 - 13:27