

Candle 4W (36W) 2700K 420lm E14 Non-Dimmable 330 deg Beam Angle

Quick Order Code: ILCANDE14NC034 / Page: 1

**Product Details**

Partcode: ILCANDE14NC034

Quick Order Code: ILCANDE14NC034

Range Name: Omni

Placement / Application: Indoor, General Lighting

Market Segment: Commercial indoor, Residential indoor

Product Type: Candle

Warranty: 2 Years

CE / RoHS: Yes

Physical Data

Lamp Base: E14

Base Type: Small Edison screw

Base Colour: Silver

Globe Type: Candle

Globe Finish: Clear

Material: Aluminium, Glass

Construction: Glass shell, Filament strip, Aluminium base

Physical Data

Length: 99mm

Width: 35mm

Weight (Unpackaged Single Unit): 15g

Lamp or Luminaire Shape: Oval

Lamp Fixing: Pendant, Wall

Electrical Data

Voltage Range: 220-240V

Power Consumption: 4.0 Watts

Driver included: Yes

Electric Current: AC

Ampage: 32.00mA

Frequency Range: 50 Hz

Power Factor: ≥ 0.40

Wattage Equivalent: 36 Watts

Dimming: Non-dimmable

LVD Certified: Yes

EN: EN-62560

Light Data

Lumens: 420lm

Lumens per Watt: 105.0lm/W

Beam Angle: 330°

Correlated Colour Temperature (CCT): 2,700k

Colour Temperature: Warm

Colour Rendering Index (CRI): ≥ 80

LED Manufacturer: Epistar

LED Type: Filament chip

Instant on - Less than 1 second: Yes

Lifetime: 15,000 hrs

Switching Cycles: $>7,500$ X

Environmental

Energy Rating: A++

Lowest Operating Temperature: -20 degrees

Maximum Operating Temperature: 40 degrees

IP (Ingress Protection) Rating: IP20

Hg 0% (Mercury Free): Yes

Packaging



EAN Barcode (unit of 1): 5055788215387

Packaged Weight (Unit of 1): 90g

Length (unit of 1): 108mm

Width (unit of 1): 42mm

Depth (unit of 1): 42mm

Outer packaging info available on website

Product data last updated on: Friday, May 13, 2016 - 13:28