

Classic Globe (GLS) Omni-Lamp 7W (60W) 2700K 806lm E27 Dimmable 330 deg Beam Angle

Quick Order Code: ILGLSE27DC036 / Page: 1

**Product Details**

Partcode: ILGLSE27DC036

Quick Order Code: ILGLSE27DC036

Range Name: Omni

Placement / Application: Indoor, General Lighting

Market Segment: Commercial indoor, Residential indoor

Product Type: GLS

Warranty: 2 Years

CE / RoHS: Yes

Physical Data

Lamp Base: E27

Base Type: Edison screw

Base Colour: Matt white

Globe Type: Classic Globe (GLS)

Globe Finish: Clear

Material: Aluminium, Glass

Construction: Glass shell, Filament strip, Aluminium base

Physical Data

Length: 140mm
Width: 60mm
Weight (Unpackaged Single Unit): 44g
Lamp or Luminaire Shape: Round
Lamp Fixing: Pendant, Wall

Electrical Data

Voltage Range: 220-240V
Power Consumption: 7.0 Watts
Driver included: Yes
Electric Current: AC
Ampage: 32.00mA
Frequency Range: 50 Hz
Power Factor: ≥ 0.70
Wattage Equivalent: 60 Watts
Dimming: Dimmable with compatible dimmers
Compatible Dimmer(s): Varilight JQP401W
LVD Certified: Yes
EN: EN-62560

Light Data

Lumens: 806lm
Lumens per Watt: 115.0lm/W
Beam Angle: 330°
Correlated Colour Temperature (CCT): 2,700k
Colour Temperature: Warm
Colour Rendering Index (CRI): ≥ 80
LED Manufacturer: Epistar
LED Type: Filament chip
Instant on - Less than 1 second: Yes
Lifetime: 15,000 hrs
Switching Cycles: $>7,500$ X

Environmental

Energy Rating: A++

Lowest Operating Temperature: -20 degrees

Maximum Operating Temperature: 40 degrees

IP (Ingress Protection) Rating: IP20

Hg 0% (Mercury Free): Yes

Packaging



EAN Barcode (unit of 1): 5055788215479

Packaged Weight (Unit of 1): 94g

Length (unit of 1): 125mm

Width (unit of 1): 64mm

Depth (unit of 1): 64mm

Outer packaging info available on website

Product data last updated on: Friday, May 13, 2016 - 13:39