

**Classic Globe (GLS) Omni-Lamp 7W (60W) 2700K 810lm B22 Dimmable 330 deg Beam Angle**

*Quick Order Code: ILGLSB22DC037 / Page: 1*

**Product Details**

Partcode: ILGLSB22DC037

Quick Order Code: ILGLSB22DC037

Range Name: Omni

Placement / Application: Indoor, General Lighting

Market Segment: Commercial indoor, Residential indoor

Product Type: GLS

Warranty: 2 Years

CE / RoHS: Yes

**Physical Data**

Lamp Base: B22

Base Type: Bayonet cap

Base Colour: Matt white

Globe Type: Classic Globe (GLS)

Globe Finish: Clear

Material: Aluminium, Glass

Construction: Glass shell, Filament strip, Aluminium base

**Physical Data**

Length: 140mm  
Width: 60mm  
Weight (Unpackaged Single Unit): 44g  
Lamp or Luminaire Shape: Round  
Lamp Fixing: Pendant, Wall

**Electrical Data**

Voltage Range: 220-240V  
Power Consumption: 7.0 Watts  
Driver included: Yes  
Electric Current: AC  
Ampage: 32.00mA  
Frequency Range: 50 Hz  
Power Factor:  $\geq 0.70$   
Wattage Equivalent: 60 Watts  
Dimming: Dimmable with compatible dimmers  
Compatible Dimmer(s): Varilight JQP401W  
LVD Certified: Yes  
EN: EN-62560

**Light Data**

Lumens: 810lm  
Lumens per Watt: 116.0lm/W  
Beam Angle: 330°  
Correlated Colour Temperature (CCT): 2,700k  
Colour Temperature: Warm  
Colour Rendering Index (CRI):  $\geq 80$   
LED Manufacturer: Epistar  
LED Type: Filament chip  
Instant on - Less than 1 second: Yes  
Lifetime: 15,000 hrs  
Switching Cycles:  $>7,500$  X

### Environmental

Energy Rating: A++

Lowest Operating Temperature: -20 degrees

Maximum Operating Temperature: 40 degrees

IP (Ingress Protection) Rating: IP20

Hg 0% (Mercury Free): Yes

### Packaging



EAN Barcode (unit of 1): 5055788215387

Packaged Weight (Unit of 1): 94g

Length (unit of 1): 125mm

Width (unit of 1): 64mm

Depth (unit of 1): 64mm

**Outer packaging info available on website**

*Product data last updated on: Friday, May 13, 2016 - 13:39*