

G9 2.5W (20W) 2700K 160lm Non-Dimmable Lamp*Quick Order Code: 414613 / Page: 1*

This 2.5W retro-fit Integral LED G9 delivers a warm light and brightness, similar to a 20W halogen bulb. Ideal for living rooms, dining rooms and bedrooms, in classic or modern ceiling lamp fittings.

Product Details

Partcode: ILG9C2.5N27KABWA

Quick Order Code: 414613

Range Name: Mensae

Product Type: G9

Warranty: 3 Years

CE / RoHS: Yes

Physical Data

Lamp Base: G9

Base Type: G9

Base Colour: Matt white

Globe Finish: Clear

Material: Silicone, Polycarbonate

Construction: Silicon, Polycarbonate, Nickel-plated brass pin

Physical Data

Length: 49mm
Width: 16mm
Weight (Unpackaged Single Unit): 10g
Lamp or Luminaire Shape: Cylindrical
Lamp Fixing: Pendant, Wall

Electrical Data

Voltage Range: 220-240V
Power Consumption: 2.5 Watts
Driver included: Yes
Driver IC Manufacturer: TDK
Electric Current: AC
Ampage: 31.00mA
Frequency Range: 50 Hz
Power Factor: ≥ 0.37
Wattage Equivalent: 20 Watts
Dimming: Non-dimmable
LVD Certified: Yes
EN: EN-62560

Light Data

Lumens: 160lm
Lumens per Watt: 64.0lm/W
Beam Angle: 270°
Correlated Colour Temperature (CCT): 2,700k
Colour Temperature: Warm
Colour Rendering Index (CRI): ≥ 80
LED Manufacturer: Epistar
LED Type: Surface mounted device (SMD)
LED Size: 2835
Instant on - Less than 1 second: Yes
Lifetime: 25,000 hrs
Switching Cycles: $>15,000$ X

Environmental

Energy Rating: A+

Lowest Operating Temperature: -25 degrees

Maximum Operating Temperature: 60 degrees

IP (Ingress Protection) Rating: IP63

Hg 0% (Mercury Free): Yes

Packaging



EAN Barcode (unit of 1): 5055788211280

Packaged Weight (Unit of 1): 11g

Length (unit of 1): 54mm

Width (unit of 1): 20mm

Depth (unit of 1): 20mm

Outer packaging info available on website

Product data last updated on: Friday, May 13, 2016 - 13:27