

0904 HSS

STEEL DRILL BITS WITH REDUCED SHANK

Universal steel drill bits for any chuck.

- ✓ Premium steel drill bits with reduced shank support drilling of larger diameters in a small chuck and with hand-held drills
- ✓ Ground HSS steel drill bit for highest precision
- ✓ Ideal for stationary drilling



SPEED LIFETIME

Art. NUMBER	Ø	FLUTE LENGTH	FLUTE LENGTH	SHANK Ø	SHANK LENGTH
21542 8	10	87	133	8	1
21544 2	11	94	142	8	1
21546 6	12	101	151	8	1
21548 0	13	101	151	8	1
21549 7	13.5	108	160	10	1
21550 3	14	108	160	10	1
21551 0	14.5	114	169	10	1
21552 7	15	114	169	10	1
21553 4	15.5	120	178	10	1
21554 1	16	120	178	10	1
21555 8	16.5	125	184	13	1
21556 5	17	125	184	13	1
21557 2	17.5	130	191	13	1
21558 9	18	130	191	13	1
21559 6	18.5	135	198	13	1
21560 2	19	135	198	13	1
21561 9	19.5	140	205	13	1
21562 6	20	140	205	13	1
23998 1	22	150	219	13	1
23999 8	25	150	246	13	1

					
CYL	Sheet metal	Non-ferrous metals	Iron	Cast iron	Steel